

## Meet the New Corning® T-75 Flask

# CELLS WON'T NOTICE THE IMPROVEMENTS IN THE CORNING FLASK. YOU WILL.

CORNING

### SAME:

- Surface treatment
- cGMP manufacturing
- Cell growth area
- Stable stacking design
- Large, clear viewing surface
- High standards of quality (100% leak tested)
- Nonpyrogenic (<0.1 EU/mL)
- BSE/TSE compliant
- Canted neck for easier pouring and pipet access

For questions, contact your local Corning Life Sciences office or Technical Support at [CLSTechServ@corning.com](mailto:CLSTechServ@corning.com).



### NEW:

#### Rounded shoulders provide:

- Improved scraping with fewer corners
- More efficient cell recovery
- Easier grip
- Better access to cap for removal and tightening
- Sterility assurance level (SAL)  $10^{-6}$

#### Pipet Divot provides:

- No-tip liquid removal
- One-handed media addition and removal
- Access for 50 mL pipets

### Ordering Information

The improved flask has a new catalog number (note the "U" at the end of the previous number)

Cat. No.	Flask Description	Qty/Pk	Qty/Cs
430641U	75 cm <sup>2</sup> canted neck, vent cap, sterile, tissue culture treated	5	100
430720U	75 cm <sup>2</sup> canted neck, plug seal cap, sterile, tissue culture treated	5	100
430725U	75 cm <sup>2</sup> canted neck, phenolic style cap, sterile, tissue culture treated	5	100
431464U	75 cm <sup>2</sup> canted neck, vent cap, sterile, not treated	5	100

**Warranty/Disclaimer:** Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.