CORNING

Lightguide Distribution Center (LDC) DWDM Module, LGX-Compatible, 20 Channel, 40-59

Corning offers a variety of DWDM modules compatible with the LDC family connector housings. Components are compliant to Telcordia requirements, including GR-1209, GR-1221, and others as appropriate to the specification. The modules are routed directly to the LDC family housing.



Part Number: DKXB31A204000ZZB50

Features	Benefits
Accommodates standard connector types	Reduces inventory
Individual connector adapters	Enables easy connector access
Integrated fiber routing and bend-radius protection	Minimizes insertion loss

Specifications

General Specifications		
Application	CATV environments, Carrier networks	
Product Type	DWDM modules	
Fiber Category	Single-mode (OS2)	


Mechanical Specifications		
Connector Configuration	LC APC	
Housing Color	Platinum	
Housing Type	LDC	
Package Dimensions	1U LGX, extended height	
Tensile Load (N)	Minimum 5	
Fiber Type	Corning [®] SMF-28e+ [®] or equivalent	
ITU Channels	40-59	

Optical Performance Characteristics						
Channel Spacing		100 GHz				
ITU Channels		Channels 40-59				
Parameter	Minimum	Typical	Maximum			
DWDM Passband Width (nm)		λ _{πυ} +/-0.125				
Upgrade Port Wavelength (nm)	Unuse	Unused channels within Channels 20-59				
Express Port Wavelength (nm)		1260-1520 and 1570-1620				
OTDR Port Wavelength (nm)		1640-1660				
DWDM Channel Insertion Loss (dB)			4.5			
Upgrade Port Insertion Loss (dB)			4.1			
Express Port Insertion Loss (dB)			2.5			
OTDR Port Insertion Loss (dB)			2.5			
DWDM Passband Ripple (dB)			0.5			
DWDM Insertion Loss Uniformity (dB)			2.0			
Test Point Insertion Loss (dB)			15.5			
DWDM Adjacent Channel Isolation (dB)	30					
DWDM Nonadjacent Channel Isolation (dB)	45					
Upgrade Port Isolation (dB)	12					
Express Channel Isolation (dB)	12					
OTDR Port Isolation (dB)	30					
Return Loss (dB)	45					
DWDM and OTDR Port Directivity (dB)	55					
Express and Upgrade Port Directivity (dB)	45					
PDL (dB)			0.30			
PMD (ps)			0.25			
Optical Power (mW)			300			

Environmental Specifications				
Operating Temperature Range (°C)	-40		85	
Operating Humidity (% RH)	5		95	
Storage Temperature (°C)	-40		85	

Corning Optical Communications

Lightguide Distribution Center (LDC) DWDM Module, LGX-Compatible, 20 Channel | CRR-1110-AEN | Page 2



Optical Layout

Ordering Information

Description	Part Number
DWDM 100 GHz 20-Channel DWDM, UPG, express, OTDR, dual test, LGX	DKXB31A204000ZZB50

Shipping Information

Units Per Delivery

CORNING

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019 Corning Optical Communications. All rights reserved. CRR-1110-AEN / May 2019