

Pipet Tip Compatibility Chart



for Corning® Lambda™ Plus and Lambda EliteTouch™ Pipettors

Pipet Tip	Cat. No.	Channels	Corning Lambda Plus Pipettor								Corning Lambda EliteTouch Pipettor												
			Single-channel				Multi-channel				Single-channel				Multi-channel								
			0.1-2 µL	0.5-10 µL	2-20 µL	10-100 µL	20-200 µL	100-1000 µL	0.5-10 µL	5-50 µL	20-200 µL	50-300 µL	0.1-2 µL	0.5-10 µL	2-20 µL	5-50 µL	10-100 µL	20-200 µL	100-1000 µL	0.5-10 µL	5-50 µL	10-200 µL	30-300 µL
Corning® DeckWorks	4125	0.1-10 µL		•						•									•				
	4135			•							•									•			
	4136	1-20 µL			•									•									
	4137	1-100 µL				•									•								
	4126	1-200 µL			•	•	•			•	•				•	•	•	•			•	•	
	4138						•				•						•				•		
	4139						•				•						•				•		
	4128	1-300 µL					•				•	•				•					•	•	
	4129	100-1000 µL								•							•						
	4140									•							•						
Isotip	4801	0.1-2 µL	•											•									
	4807	0.2-10 µL	•	•						•				•	•				•				
	4808	0.5-10 µL		•						•				•					•				
	4821	1-30 µL			•										•								
	4823	1-200 µL					•				•				•					•			
	4809	100-1000 µL								•						•							
Axygen® MultiRack	MR-10XT*	0.1-10 µL		•						•				•					•				
	MRF-10XT*			•							•				•				•				
	MRF-20	1-20 µL			•									•									
	MRF-100	1-100 µL				•								•	•								
	MR-200	1-200 µL				•	•				•				•	•					•		
	MRF-200XT*					•	•				•				•	•					•		
	MRF-200NX					•					•				•						•		
	MRF-300XT*	1-300 µL				•					•	•			•						•	•	
	MR-300XT*					•					•	•			•						•	•	
	MR-300					•					•	•			•						•	•	
	MR-1000XT*	50 - 1250 µL								•							•						
	MRF-1000XT*									•							•						
Universal Fit	T-300	0.5-10 µL	•	•						•				•	•				•				
	TF-300		•	•						•				•	•				•				
	TF-20	0.5-20 µL			•									•									
	TF-50	0.5-50 µL								•				•					•				
	TF-100	1-100 µL				•								•									
	TR-222	1-200 µL				•	•				•				•	•	•			•	•		
	TF-200						•				•					•					•		
	T-350	1-300 µL									•	•									•	•	
	TF-350						•				•	•									•	•	
	T-1000	100-1000 µL									•						•						
	TF-1000										•						•						
	TF-1200	100-1100 µL								•							•						

*Extended length tip

NOTE: Corning pipettors are calibrated using non-filtered tips, thus pipettor recalibration might be required when using filter tips.

	Non-filtered Pipet Tip	Cat. No.	Volume Range	Corning® Lambda™ Plus Pipettor								Corning Lambda EliteTouch™ Pipettor													
				Channels				Single-channel				Multi-channel				Single-channel				Multi-channel					
				0.1-2 µL	0.5-10 µL	2-20 µL	10-100 µL	20-200 µL	100-1000 µL	0.5-10 µL	5-50 µL	20-200 µL	50-300 µL	0.1-2 µL	0.5-10 µL	2-20 µL	5-50 µL	10-100 µL	20-200 µL	100-1000 µL	0.5-10 µL	5-50 µL	10-200 µL	30-300 µL	
Eppendorf	epT.I.P.S.®	-	2-200 µL				•	•																	
			20-300 µL																					•	
			50-1000 µL																						
Gilson	Diamond®	-	0.1-10 µL		•																				
			0.1-20 µL																						
			2-200 µL					•	•																
			20-300 µL																						•
			100-1000 µL																						
BrandTech	Standard	-	0.1-20 µL			•																			
			5-300 µL																						
			50-1000 µL																						•
Sartorius	Optifit®	-	0.1-10 µL		•																				
			0.5-200 µL					•	•																
			5-350 µL																						•
			10-1000 µL																						
Starlab	TipOne®	-	0.1-10 µL		•																				
			1-200 µL					•	•	•															
			1-300 µL																						•
			100-1000 µL																						
ThermoFisher	Finntip®	-	5-200 µL					•	•																
			5-300 µL																					•	
			100-1000 µL																						

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.

CORNING

Corning Incorporated
Life Sciences

www.corning.com/lifesciences

NORTH AMERICA
t 800.492.1110
t 978.442.2200

ASIA/PACIFIC
Australia/New Zealand
t 61 427286832
Chinese Mainland
t 86 21 3338 4338

India
t 91 124 4604000
Japan
t 81 3-3586 1996
Korea
t 82 2-796-9500
Singapore
t 65 6572-9740
Taiwan
t 886 2-2716-0338

EUROPE
CSEurope@corning.com
France
t 0800 916 882
Germany
t 0800 101 1153
The Netherlands
t 020 655 79 28
United Kingdom
t 0800 376 8660

All Other European Countries
t +31 (0) 206 59 60 51

LATIN AMERICA
grupola@corning.com
Brazil
t 55 (11) 3089-7400
Mexico
t (52-81) 8158-8400