

OptiSheath® Multidwelling Unit (MDU) Terminal with Multifiber Hardened Connectorized Stubs



OptiSheath MDU Terminal with four OptiTip stub cables (open)



OptiSheath MDU Terminal with four OptiTip stub cables (closed)

The OptiSheath® MDU terminal is a rugged, indoor/outdoor low-profile interconnect between the distribution network and indoor/outdoor drop cables for multidwelling unit applications. FlexNAP™ adapter is compatible with up to four 12-fiber Pushlok™ or OptiTip® stub cables for fast-and-easy connectivity.

The field-friendly, multilayer design allows installers to access only the terminal components necessary for initial installation or subscriber turn-up.


Features	Benefits
SC or LC connector technology available with Pushlok or OptiTip-enabled, prestubbed input cables	Enables quick, easy, and reliable FlexNap system connections
Available with or without spliced pigtailed	Allows splicing in the field or direct termination in both preconnectorized or field-connectorized drops
Flame-retardant, impact-resistant, engineering-grade thermoplastic and hinged cover with padlock	Maximizes product lifetime and security
Flexible design with multiple stub and drop options, including a Pushlok or OptiTip adapter input interface	Provides solutions for a variety of MDU installations
Protective coverings for incoming and drop cables	Indoor/outdoor plastic or metal skirt available to protect incoming and drop cables

Standards	
Design and test criteria	Terminals tested and qualified to applicable sections of Telcordia GR-771. Listed to UL, 94-V0

OptiSheath® MDU Terminal, OptiTip® Stubs

Specifications	
Weight	6.5 lb (3 kg)
Dimensions (H x W x D)	16.29 x 14.59 x 6.0 in (41.4 x 37.1 x 15.2 cm)
Subscriber Connection	12, 24, 36, 48
Door	One
Connectors	SC APC, SC UPC, LC APC, and LC UPC
Drop Connection	Compatible with 1.65- to 4.8-mm drop cables, preconnectorized, field connectorized at the MDU terminal
Color	Cool Gray
Distribution	Up to 48, SC APC drop ports
Mounting Type	Wall mountable

Ordering Information



1 Select cable fiber count.

- 24 = 24 fibers
- 36 - 36 fibers
- 48 = 48 fibers

Note: M1 stubbed cables have 12 fibers per OptiTip® connector, up to a maximum of four cables

3 Select number of ports. (same as cable fiber count)

- 24 = 24 ports
- 36 = 36 ports
- 48 = 48 ports

6 Select special configuration.

- M1 = Stubbed with non-pinned OptiTip, 4 max
- M2 = Stubbed with pinned OptiTip, 4 max
- T1 = Stubbed with Pushlok™ MT Pinned connector, 4 max
- T2 = Stubbed with Pushlok MT Nonpinned connector, 4 max

2 Select cable length.

- 31 = 100 ft
- 61 = 200 ft
- 92 = 300 ft
- F3 = 500 ft
- Q4 = 800 ft
- W5 = 1,000 ft

4 Select connector type.

- 6C = SC APC
- 3C = SC UPC
- B3 = LC APC
- A9 = LC UPC

7 Select shipping package.

- 2 = Used on all stubless and stubbed units with a stubbed cable length of 500 ft or less.
- R = Recommended on all stubbed terminals with a stub length greater than 500 ft. Ships on a reel.

5 Select input cable type.

- B4 = SST flat dielectric drop cable
- BZ = I/O LSZH™, SST flat drop (FR)
- B1 = Toneable SST flat drop

8 Select drop connection.

- Q = Preconnectorized or field-connectorized drops
- P = Configured for pigtail splicing

For additional options, contact a Corning Customer Care Representative at 800-743-2675.

OptiSheath® MDU Terminal, OptiTip® Stubs Accessories



OptiSheath MDU Terminal Indoor/Outdoor Skirt



OptiSheath MDU Terminal Mounting Bracket

The indoor/outdoor protective skirt kit allows the removal and installation of the skirt without tools after initial installation. The cavity created by the skirt and mounting bracket features allow both cable management and storage for the incoming and drop cables.

Part Number	Product Description	Units per Delivery
MDU-PLAS-SKRT-FR	Indoor/outdoor plastic protective skirt	1/1
MDU-PLAS-BRKT-FR	Indoor/outdoor plastic skirt mounting bracket	1/1
MDU-PLAS-SKRT-BRKT-FR	Indoor/outdoor plastic skirt and mounting bracket kit	1/1
MDU-SKRT-U3	Metal, protective U-Guard for incoming drops and cables	1/1
MDU-CC-BT-KIT	Corning® ClearCurve® cable, 4.8-mm rugged drop MDU installation kit* (quantity for 10 MDUs)	1/1
MDU-SLACK-KIT	Metal slack storage unit that mounts on the back of the MDU terminal	1/1

*Kit includes watertight fittings to seal incoming drops, braided tubing for protecting and routing slack when splicing in 4.8-mm drops and filler cords to seal inputs when using fewer than eight drops per input

CORNING

**Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm**

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification.
A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners.
Corning Optical Communications is ISO 9001 certified. © 2015, 2024 Corning Optical Communications. All rights reserved. CRR-1558-AEN / April 2024