Features and Benefits

Small diameter and bend radius

Easy installation in space-constrained areas

All-dielectric cable construction Requires no grounding or bonding

Polyurethane outer jacket Environmental and mechanical protection

Flexible Facilitates portability


Standards

Design and Test Criteria

MLF-PRF-85045F and MIL-PRF-85045F/8A Corning outdoor tactical fiber optic cable is ideal for connecting modular telecommunications gear for secure, dependable communications, data or video. Applications include military mobile communications (temporary or permanent communication systems), traffic and video control (optical feeds in rugged environments), broadcast video (temporary or permanent setups at events), and industrial or other harsh environments (extreme conditions such as abrasive or chemical atmospheres and high crush environments).

This flexible cable uses 900 µm buffered fibers surrounded by dielectric strength members and is protected by a rugged polyurethane outer jacket that provides superior environmental and mechanical protection. The flexibility facilitates portability through deployment and retraction of the cable onto a reel. The all-dielectric cable construction requires no grounding or bonding, while the small diameter and bend radius allow easy installation in space-constrained areas. A TEMPEST rating is also available for this cable. This cable cannot be permanently installed aerially or above grade, however temporary installations that are aerial or above grade are acceptable. Corning optical fiber and the tactical fiber optic cable are manufactured in the United States.





CORNING

Family Spec Sheet 0109_NAFTA_AEN Page 1 | Revision date 2015-10-07

CORNING




Tactical Fiber Optic Cable | Photo LAN757

Specifications

Temperature Range	
Storage	-57 °C to 85 °C (-71 °F to 185 °F)
Installation	-46 °C to 71 °C (-51 °F to 160 °F)
Operation	-46 °C to 71 °C (-51 °F to 160 °F)

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Dia- meter	Product Type	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Min. Bend Radius Instal- lation	Min. Bend Radius Ope- ration	Weight
2	5.8 mm (0.2 in)	Dielectric	1450 N (327 lbf)	290 N (65 lbf)	58 mm (2.3 in)	29 mm (1.1 in)	28.2 kg/km (19 lb/1000 ft)
4	6.0 mm (0.2 in)	Dielectric	1500 N (337 lbf)	300 N (67 lbf)	60 mm (2.4 in)	30 mm (1.2 in)	31.3 kg/km (21 lb/1000 ft)
6	7.0 mm (0.3 in)	Dielectric	1750 N (393 lbf)	350 N (79 lbf)	70 mm (2.8 in)	35 mm (1.4 in)	40 kg/km (27 lb/1000 ft)
12	8.0 mm (0.31 in)	Dielectric	2000 N (450 lbf)	400 N (90 lbf)	80 mm (3.1 in)	40 mm (1.6 in)	53 kg/km (36 lb/1000 ft)





CORNING

Chemical Characteristics

RoHS

Free of hazardous substances according to RoHS 2002/95/ EG

Transmission Performance


Multimode				
Fiber Core Diameter (µm)	50	50	50	
Fiber Category	OM2	OM3	OM4	
Fiber Code	Т	Т	Т	
Performance Option Code	31	80	90	
Wavelengths (nm)	850/1300	850/1300	850/1300	
Maximum Attenuation (dB/km)	3.0/1.0	3.0/1.0	3.0/1.0	
Serial 1 Gigabit Ethernet (m)	750/600	1500/500	1000/600	
Serial 10 Gigabit Ethernet (m)	150/-	2000/-	550/-	
Min. Overfilled Launch (OFL) Bandwidth (MHz*km)	700/500	1000/600	3500/500	
Minimum Effective Modal Bandwidth (EMB) (MHz*km)	950/-	300/-	4700/-	

* 50 μm multimode fiber (OM3/OM4) meets 0.75 ns optical skew when used in all Corning Plug & Play™/EDGE™ systems solutions.

* 50 µm multimode fiber (OM4) T90 10 Gigabit Ethernet distance assumes 1.0 dB maximum total connector/splice loss.

Single-mode		
Fiber Name	ClearCurve [®] LBL	
Fiber Category	G.657.A2/G.657.B2	
Fiber Code	J	
Performance Option Code	31	
Wavelengths (nm)	1310/1383/1550	
Maximum Attenuation (dB/km)	0.65/0.65/0.5	





Ordering Information | Note: Contact Customer Care at 1-800-743-2675 for other options.



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2015 Corning Optical Communications. All rights reserved.



CORNING